

MAXIMUM WORKING DEPTH: 100 METRES/328 FEET. WHERE THE FREE END OF THE CABLE IS TO BE TERMINATED IN A SUBMERGED POSITION, ADEQUATE SEALING MUST BE PROVIDED TO PROTECT CONNECTIONS.

THE PUSH-ROD RETRACTS A FURTHER 4mm NOM. FROM START OF CALIBRATED TRAVEL. STANDARD VERSIONS THE PUSH-ROD EXTENDS A FURTHER 8mm NOM. FROM END OF CALIBRATED TRAVEL, FOR SPRUNG VERSIONS: 'R': 1mm, 'S': 2mm. 'V' CODED PUSH-ROD WILL DEPART SENSOR BODY.

K	RAN1037 WITHDRAWN	PDM
L	RANGE WAS 50-600mm RAN1056	RDS
М	OPTION 'S' ADDED ~ RAN1108	PDM
N	5-CORE OPTION ADDED ~ RAN1102	PDM

Herbertek www.herbertek.se info@herbertek.se +46-18 590510

ELECTRICAL OPTIONS/ SPECIFICATIONS <u>OUTPUT</u> 0.5 TO 4.5V RATIOMETRIC 57 SUPPLY CURRENT 12mA TYP. 20mA MAX.

CABLE: 0.2mm², O/A SCREEN, PUR JACKET - SUPPLIED WITH 50cm OR REQUIRED LENGTH IN cm (15000cm MAX). STANDARD 3-CORE: JACKET Ø4mm BLACK e.g. 'L50' OPTIONAL 5-CORE: JACKET Ø4.6mm BLUE e.g. 'LQ50' CONNECTIONS;

3 CORE 5 CORE RED RED

ORG +SENSE (5-WIRE ONLY) BLACK BI ACK OV -SENSE (5-WIRE ONLY) GRY

WHITE WHITE OUTPUT SCREEN SCREEN BODY

RANGE OF DISPLACEMENT FROM 5mm TO 800mm, IN INCREMENTS OF 1mm.


BODY MATERIAL: STAINLESS STEEL 316.

FURTHER OPTIONS:

SINGLE PAIR OF BODY CLAMPS 'P' TWO PAIRS OF BODY CLAMPS 'P2'

SPRING RETURN PUSH-ROD, TRAVEL ≤300mm RETURN TO EXTENDED POSITION (CODE 'R') RETURN TO RETRACTED POSITION (CODE 'S')

PUSH-ROD FREE (CODE 'V') - NOT AVAILABLE WITH SPRUNG OPTIONS.



NOTE:- READ INSTALLATION SHEET X115-19 FOR FULL INSTRUCTIONS FOR USE.

ATEX / IECEX APPROVED TO **⟨**E_X**⟩** II 1G

Ex ia IIC T4 Ga (Ta= -40° to +80°C) Ui 11.4V, li 0.2A, Pi 0.51W

APPROVED FOR USE IN CONJUNCTION WITH A GALVANICALLY ISOLATED BARRIER.

NOTE: APPROVAL ONLY APPLIES AT NORMAL ATMOSPHERIC PRESSURE!



K	16/10/15	4 1	CHECKED BY		
L	09/11/15	((()) (()	PDM	X.X ±0.2 X.XX ±0.1	
М	14/09/16	7		DIMS mm	
N	24/04/17	DESCRIPTION			
		INTRINSICALLY SAFE RUGGED			
		SUBMERSIBLE STAND-ALONE			
		LINEAR POSITION SENSOR			
SCALE 13mm		DRAWING >	(115-11	REV N	
		SHEET 1 OF 1			

DRAWINGS NOT TO BE CHANGED WITHOUT REFERENCE TO THE CHANGE PROCEDURE. CHANGES TO PARTS USED IN INTRINSICALLY SAFE PRODUCT MUST BE APPROVED BY THE AUTHORISED PERSON THIS IS AN UNCONTROLLED PRINT AND WILL NOT BE UPDATED.